NOTES:

1. SUBSTRATE MATERIAL:

N-BK7

- 2. SURFACE S1 TO BE PARALLEL WITH SURFACE S2 TO WITHIN ≤ 3 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: 50% R ±5% @ 550nm 50% T ±5% @ 550nm


S2: AR R(avg) ≤1%, R(abs) ≤2% @ 400 - 700nm

4.

CUT WITH 0.25mm MAXIMUM EDGE CHIP

5. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
ANGLE OF INCIDENCE	45°	45°
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm

	Edmund Option	CS®

THIRD ANGLE PROJECTION		TITLE	25 x 25mm, 50 R/50 T, PLATE BEAMSPLITTER	
ALL DIMS IN	mm	DWG NO	48902	SHEET 1 OF 1