

NOTES:


1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold (700-10000nm)

R(AVG) >96% @ 700 - 2000nm

R(AVG) >96% @ 2000 - 10,000nm

S2: NONE
3. EDGES GROUND
4. RoHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div><div>EO[®]</div><div>Edmund Optics[®]</div></div></div>			
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> <div></div>	TITLE	20mm Dia Protected Gold, 4-6λ Mirror	
SURFACE QUALITY	60-40	N/A		DWG NO	43732	SHEET 1 OF 1
SURFACE FLATNESS	4 - 6λ	N/A				
CLEAR APERTURE	Ø 19.00	N/A	ALL DIMS IN	mm		
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				