


NOTES:

1. SUBSTRATE MATERIAL:  
BOROFLOAT®
2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1: NONE  
S2: NONE
3. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4.

FINE GROUND SURFACE
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	CONCAVE	PLANO				
EFFECTIVE FOCAL LENGTH	1143mm	N/A				
FOCAL LENGTH TOLERANCE	±2%	N/A				
APERTURE	f/10.6	N/A				
SURFACE QUALITY	60-40	60-40				
SURFACE FLATNESS	λ/8	λ/8				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				

THIRD ANGLE PROJECTION		TITLE		DWG NO		SHEET	
ALL DIMS IN		Ø4.25in, 45in FL UNCOATED, SPHERICAL MIRROR		32083		1 OF 1	
mm							

Edmund Optics®