## NOTES:


- 1. SUBSTRATE: FUSED SILICA
- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(AVG) ≤ 1.5% FROM 250-700nm R(ABS) ≤ 1.0% FROM 350-450nm

FOR INFORMATION ONLY:

PARTS TO THIS DRAWING

DO NOT MANUFACTURE

- 4. FINE GRIND SURFACE
- 5. Rohs Compliant



	S1	\$2					
SHAPE	PLANO	PLANO			TITLE	25mm DIA., 4mm THICK, UV-VIS COATED, λ/4 FUSED SILICA WINDOW	
SURFACE QUALITY	40-20	40-20					ILD,
CLEAR APERTURE (mm)	Ø22.50	Ø22.50		1			CULET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	14977	Sheet 1 Of 1