

NOTES:

- 1. SUBSTRATE: **FUSED SILICA**
- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(ABS) ≤ 0.25% AT 880nm R(AVG) ≤ 1.25% FROM 400-870nm R(AVG) ≤ 1.25% FROM 890-1000nm

FINE GRIND SURFACE

5. Rohs Compliant





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHEET

1 OF 1

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	40-20	40-20		
CLEAR APERTURE (mm)	Ø22.50	Ø22.50		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

		G	Edmund Option	S®
IHIKD ANGLE / A \ C TITLE		25mm DIA., 4mm THICK, VIS-NIR COA λ/4 FUSED SILICA WINDOW	TED,	
ALL DIMS IN	mm	DWG NO	14990	SHEE

14990