
NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE

5. Rohs Compliant





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

4.8

/4\

-4.00±0.20

-S2

S1-

R

— 1

| | S1 | \$2 | | | | | |
|---------------------|----------------------|----------------------|-------------|----|--------|---|-----------------|
| SHAPE | PLANO | PLANO | THIRD ANGLE | | TITLE | 25.4mm DIA., 4mm THICK, VIS 0° COATED λ/4 N-BK7 WINDOW | |
| SURFACE QUALITY | 60-40 | 60-40 | | | | | |
| CLEAR APERTURE (mm) | Ø22.86 | Ø22.86 | | | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO | 15433 | SHEET 1 OF 1 |

