## NOTES:

- SUBSTRATE: GRADE A FINE ANNEALED 1. SCHOTT: N-BK7 517/642
- 2. **ROHS COMPLIANT**
- 3. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN 3 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE) SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION 4.

 $R(abs) = 50\% \pm 5\% @ 550nm$ 

 $R(abs) = 50\% \pm 10\%$  FROM 400-700nm

 $T(abs) = 50\% \pm 5\% @ 550nm$ 

 $T(abs) = 50\% \pm 10\%$  FROM 400-700nm

VISUÁL COLOR = NEUTRAL

S2: BBAR


R(abs) ≤ 2.0% FROM 400-700nm R(avg) ≤ 1.0% FROM 400-700nm

/5.\

FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE



## PARTS TO THIS DRAWING

	\$1	S2 PLANO			
SHAPE	PLANO				
SURFACE ACCURACY AT 632.8nm (P-V)	1 WAVE	1 WAVE			
SURFACE QUALITY	60 - 40	60 - 40			
SURFACE FLATNESS	2λ PER 25mm	2λ PER 25mm			
MIN CLEAR APERTURE	10.63 x 14.88	10.63 x 14.88			
MIN COATING APERTURE	10.63 x 14.88	10.63 x 14.88			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			<b>Edmund Optics</b> ®		CS <sup>®</sup>
THIRD ANGLE PROJECTION		TITLE	BS VIS 50R/50T 12.5X17.5MM 1MM THK		
	ALL DIMS IN	mm	DWG NO	35941	SHEET 1 OF 1