

NOTES:

1. SUBSTRATE: GRADE A FINE ANNEALED
SCHOTT: N-BK7 517/642
2. ROHS COMPLIANT
3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN
4. COATING (APPLY ACROSS COATING APERTURE)
SPECIFICATIONS AT 45° AOI AND RANDOM POLARIZATION
S1:
 $R(\text{abs}) = 70\% \pm 5\% @ 550\text{nm}$
 $R(\text{abs}) = 70\% \pm 10\% \text{ FROM } 400\text{-}700\text{nm}$
 $T(\text{abs}) = 30\% \pm 5\% @ 550\text{nm}$
 $T(\text{abs}) = 30\% \pm 10\% \text{ FROM } 400\text{-}700\text{nm}$
 VISUAL COLOR = NEUTRAL


S2: BBAR
 $R(\text{abs}) \leq 2.0\% \text{ FROM } 400\text{-}700\text{nm}$
 $R(\text{avg}) \leq 1.0\% \text{ FROM } 400\text{-}700\text{nm}$



FINE GRIND SURFACE



MARK IDENTIFIES BEAMSPLITTER SURFACE




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

	S1	S2
SHAPE	PLANO	PLANO
SURFACE ACCURACY AT 632.8nm (P-V)	1 WAVE	1 WAVE
SURFACE QUALITY	60 - 40	60 - 40
SURFACE FLATNESS	2λ PER 25mm	2λ PER 25mm
MIN CLEAR APERTURE	21.25 x 21.25	21.25 x 21.25
MIN COATING APERTURE	21.25 x 21.25	21.25 x 21.25
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 	TITLE	BS VIS 70R/30T 25X25MM 1MM THK	
ALL DIMS IN	mm	DWG NO	35952
			SHEET 1 OF 1