




NOTES:

- 1. SUBSTRATE:
D-ZK3
- 2. NUMERICAL APERTURE: 0.24
- 3. COATING
S1 & S2: R(AVG) ≤ 0.5% @ 350 - 700nm
- 4. FOCAL LENGTH TOLERANCE: ±1%
- 5. TRANSMITTED WAVEFRONT ERROR (λ, RMS): < 0.087



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			EFL	11.00	 Edmund Optics®		
			BFL	9.30			
SHAPE	S1 CONVEX	S2 PLANO			TITLE	0.24 NA 11.00mm FL 350-700nm AR Coated, Molded Aspheric Lens	
SURFACE QUALITY	80-50	80-50					
CLEAR APERTURE	Ø5.40	Ø5.40					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	37109	SHEET 1 OF 1