
## NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. P1 PARALLEL TO P2 <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1: R(avg)= 50% ± 10% @ 400 700nm R(abs)= 50% ± 5% @ 550nm T(avg)= 50% ± 10% @ 400 - 700nm T(abs)= 50% ± 5% @ 550nm
  - S2: R(avg) ≤1.0% @ 400 700nm R(abs) ≤2.0% @ 400 - 700nm



5. ROHS COMPLIANT



## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

## SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A \$1 \$2				<b>Edmund Optics</b> *			
SHAPE	PLANO	PLANO			TITLE	25 x 35.36 x 1mm, VIS, ELLIPTICAL PLATE BEAMSPLITTER	
SURFACE QUALITY	60-40	60-40					
SURFACE FLATNESS	2λ per inch	2λ per inch					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	all DIMS IN	mm	DWG NO	48915	SHEET 1 OF 1