

NOTES:

1. SUBSTRATE MATERIAL:
N-SF5

2. COATING (APPLY ACROSS CLEAR APERTURE)



S1: ENHANCED ALUMINUM
R(avg) >95% @ 450 - 650nm

S2: NONE

3. POWER, IRREGULARITY, SURFACE QUALITY AND COATING
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

4. FINE GRIND SURFACE


5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	CONVEX	PLANO
RADIUS	12.11	INFINITY
EFFECTIVE FOCAL LENGTH	-6.1mm	N/A
FOCAL LENGTH TOLERANCE	±2%	N/A
SURFACE QUALITY	60-40	COMMERCIAL POLISH
CLEAR APERTURE	0.9	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



EO® Edmund Optics®

TITLE	Ø12mm, -6.1mm FL ENHANCED ALUMINUM, CONVEX SPHERICAL MIRROR
DWG NO	64055
SHEET	1 OF 1

ALL DIMS IN mm