



NOTES:

1. SUBSTRATE: UV GRADE FUSED SILICA
2. COATING (APPLY ACROSS COATING APERTURE)
 S1 & S2: RABS $\leq 1.0\%$ @ 250 - 425nm
 RAVG $\leq 0.75\%$ @ 250 - 425nm
 RAVG $\leq 0.5\%$ @ 370 - 420nm
3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCSEC

4. FINE GRIND SURFACE


5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 20-10 | 20-10 |
| CLEAR APERTURE | $\varnothing 40.00$ | $\varnothing 40.00$ |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

EO® Edmund Optics®

| | | | |
|--------|---|-------|--------|
| TITLE | 50mm DIA., 5mm THICK, UV-AR COATED $\lambda/10$ FUSED SILICA WINDOW | | |
| DWG NO | 65878 | SHEET | 1 OF 1 |