




NOTES:

- 1. SUBSTRATE:
Fused Silica (Corning 7980)
- 2. TEMPERATURE RANGE:
-40 TO +170 °C

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SPECTRAL RANGE	200 - 1500nm
CLEAR APERTURE	Ø45.7 ± 0.1
DIFFUSING ANGLE	0.5 ±3°
TRANSMISSION EFFICIENCY	90%

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

Edmund Optics®

TITLE

30° DIFFUSING ANGLE 50mm DIA., UV
HOLOGRAPHIC DIFFUSER

DWG NO

48520

SHEET
1 OF 1