



NOTES:

1. SUBSTRATE: PMMA
2. WAVELENGTH RANGE (nm): 400 - 700
3. EXTINCTION RATIO: 9000:1
4. OPERATING TEMPERATURE (°C): -40 to +80
5. TRANSMISSION (%):  
Single: 42  
Parallel: 36  
Crossed: < 0.004
6. RoHS: COMPLIANT


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THE POLARIZERS CONSISTS OF A POLYMER POLARIZATION  
FILM LAMINATED ONTO PMMA.

THIRD ANGLE PROJECTION 		TITLE	500 x 600mm Linear Plastic Polarizer, Unmounted	
ALL DIMS IN	mm	DWG NO	86200	SHEET 1 OF 1