


NOTES:



- 1. SUBSTRATE:
N-BK7
- 2. S2 TO BE PARALLEL TO S1 TO WITHIN <3 ARCMINS
- 3. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: 532nm Laser AR Coating
R(ABS) < 0.25% @ 266nm @ 0° AOI
- DAMAGE THRESHOLD
PULSED: 3J/cm² @ 20ns, 20Hz @ 266nm

- 4. FINE GROUND SURFACE
- 5. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACE
- 6. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY
ACROSS CLEAR APERTURE
- 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO	 Edmund Optics®			
SURFACE QUALITY	10-5	10-5				
SURFACE FLATNESS	0.10 WAVE	0.10 WAVE	TITLE Ø38.1mm x 9.53mm 532nm N-BK7 LASER WINDOW			
MIN CLEAR APERTURE	Ø34.29	Ø34.29				
MIN COATING APERTURE	Ø34.29	Ø34.29	DWG NO 38964			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			THIRD ANGLE PROJECTION 			
			ALL DIMS IN mm	SHEET 1 OF 1		