

1. CONSTRUCTION: MOUNTED IN BLACK ANODIZED RING
2. COATING (APPLY ACROSS COATING APERTURE)

PERFORMANCE SPECIFICATIONS:

FWHM: 26 NOMINAL




REFLECTION %: >99.5

TRANSMISSION %: 280 - 300nm: Tavg >50; 300 - 700nm: Tavg >90

3. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

4. TRANSMITTED WAVEFRONT DISTORTION RMS@ $<1\lambda$


5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 				
SHAPE	PLANO	PLANO			TITLE	355nm, 25mm Dia., OD 6 Blocking Notch Filter	
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	39387	
CLEAR APERTURE	Ø21.21	Ø21.21					SHEET 1 OF 1