NOTES:

1. SUBSTRATE:

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

N-BK7

- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)

S1: NONE S2: NONE

EDGES: FINE GROUND

- 5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY **ACROSS CLEAR APERTURE**
- 6. TRANSMITTED WAVE FRONT OVER THE CLEAR APERTURE SHALL BE SPHERICAL (Y⁴) +0.25λ WAVE PEAK TO VALLEY @ 587nm. WAVE FRONT ERROR FROM IDEAL SPHERICAL FORM SHALL BE LESS THEN ±0.0625 WAVES




$$Z(Y) = \frac{\left(\frac{1}{RADIUS}\right)^{*}Y^{2}}{1 + \sqrt{1 - (1 + k)^{*}\left(\frac{1}{RADIUS}\right)^{2} * Y^{2}}} + D*Y^{2} + E*Y^{4} + F*Y^{6} + G*Y^{8} + H*Y^{10} + J*Y^{12} + L*Y^{10} + Y^{10} +$$

8. APPLY AN ARROW POINTING TOWARDS THE ASPHEREIC SURFACE S2 WITH PENCIL OR PERMANENT INK

COEFFIECIENT TABLE 7.					
S 1	S2				
0	0				
0	0				
0	-1.7744384E-08				
0	0				
0	0				
0	0				

	\$1	\$2
SHAPE	PLANO	PLANO
CLEAR APERTURE	>85	>85
SURFACE QUALITY	60-40	60-40
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1



THIRD ANGLE PROJECTION	$\phi \lhd$	TITLE	25mm Dia +0.25λ Aberration, Spherical Aberration Plate	
ALL DIMS IN	mm	DWG NO	66755	SHEET