



FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $15,26$

1 AR COATING: 1550nm V-COAT
 $R(\text{ABS}) < 0,25\% @ 1550\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$8,252 \pm 0,008 \text{ CX}$	GLASS FUSED SILICA 458/678	R	$\infty \text{ PL}$
Øe	11		Øe	11
3/	$3 (0,5) \lambda = 632,8 \text{ nm}$		3/	$3 (0,5) \lambda = 632,8 \text{ nm}$
4/	-		4/	$2,18'$
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 12mm Dia, x 18mm FL 1550nm V-Coat, UV PCX Lens

DWG NO 34156

SHEET SIZE A4
 SHEET 1 OF 1