



NOTES:

1. SUBSTRATE:
Alumosilicate Glass Embedded with Silver Ions
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: BBAR (450-700nm)
R(AVG) < 0.7%, 0 - 30°
3. EFL: 0.88
4. f/# : 0.88
5. NUMERICAL APERTURE: 0.54
6. DESIGN WAVELENGTH: 670nm
7. WORKING DISTANCE: 0mm ±0.02
8. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø0.9	Ø0.9

THIRD ANGLE PROJECTION

ALL DIMS IN

mm



Edmund Optics®

1.0mm Dia, 670nm DWL, 0.0mm WD, VIS
Coated, GRIN Lens

TITLE

DWG NO

64535

SHEET
1 OF 1