


NOTES:

1. SUBSTRATE:
Fused Silica
2. SURFACE S1 TO BE PARALLEL TO SURFACE S2 TO WITHIN <3 ARCMINS
3. COATING (APPLY ACROSS COATING APERTURE)

S1: R(ABS) >99.8% @ 1030nm
DAMAGE THRESHOLD,
PULSED: 15 J/cm² @ 1030nm, 20ns, 20Hz

S2: NONE


4. FINE GROUND SURFACE
5. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACE
6. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
7. ARROW ON EDGE WITH LASER ETCH, PENCIL, OR PERMANENT INK POINTS TOWARDS SURFACE S1



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 | | | | |
|----------------------|----------------------|----------------------|--|--|--|--|
| SHAPE | PLANO | PLANO | | | | |
| SURFACE QUALITY | 10-5 | COMMERCIAL POLISH | | | | |
| SURFACE FLATNESS | 0.10 WAVE | N/A | | | | |
| MIN CLEAR APERTURE | 10.80 x 16.24 | N/A | | | | |
| MIN COATING APERTURE | 10.80 x 16.24 | N/A | | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | | | | |

| | | | | | |
|--------------------------------------------------------------------------------------------------------------|----|--------|-------|---------------------------------------------------------|--|
| THIRD ANGLE PROJECTION  | | TITLE | | 12.7 x 19.1mm 1030nm 0-45°, Yb:YAG Laser Line Mirror | |
| ALL DIMS IN | mm | DWG NO | 11312 | SHEET 1 OF 1 | |

 **Edmund Optics®**