NOTES:


- 1. SUBSTRATE: FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <3 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE)
 S1: Laser V-Coat (355nm)
 R(ABS) <0.25% @ 355nm @ 0 ±5° AOI


DAMAGE THRESHOLD, PULSED: 7.5 J/cm² @ 355nm, 20ns, 20Hz

S2: NONE

4. FINE GRIND SURFACE

5. ROHS: COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2				Edmund Option	CS®
SHAPE	PLANO	PLANO		Í		12.7mm Dia. 355nm, Nd:YAG Laser Line	Ream
SURFACE QUALITY	10-5	10-5	THIRD ANGLE PROJECTION	\bigcirc	TITLE	Sampler	Dodin
CLEAR APERTURE	90 %	90 %				o ampier	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	39001	SHEET 1 OF 1