

FOCAL LENGTH (EFL):  $10 \pm 0,1$

BACK FOCAL LENGTH (BFL): 8,18

1 AR COATING: 532nm V-COAT  
 R(ABS) < 0,25% @ 532nm @ 0° AOI

| LEFT SURFACE |                            | MATERIAL             | RIGHT SURFACE |                            |
|--------------|----------------------------|----------------------|---------------|----------------------------|
| R            | 7,85±0,008 CX              | GLASS N-SF11 785/258 | R             | $\infty$ PL                |
| Øe           | 9                          |                      | Øe            | 9                          |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                      | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                      | 4/            | 3,82'                      |
| 5/           | 40 - 20 (MIL-PRF-13830B)   |                      | 5/            | 40 - 20 (MIL-PRF-13830B)   |
| 6/           | -                          |                      | 6/            | -                          |

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT    SCALE: NONE     $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 10,0mm Diameter x 10,0mm FL, 532nm V-Coat, PCX Lens

DWG NO 69378

SHEET SIZE A4 SHEET 1 OF 1