

300 GROOVES, 25 X 25MM HIGH PERFORMANCE REFLECTION GRATING 1200nm • #37-130


- $\lambda/4$ Wave Reflected Wavefront
- Superior Dimensional Tolerances
- Groove Spacing Tolerance <0.05%



Groove Density (grooves/mm):	300
Blaze Wavelength (nm):	1200.00
Blaze Angle:	10.4°
Dimensions (mm):	25.0 x 25.0
Dimensional Tolerance (mm):	±0.1
Clear Aperture (%):	>90
Coating:	Bare Aluminum
Construction:	Ruled Grating
Substrate:	Float Glass

Thickness (mm):	6.00
Thickness Tolerance (mm):	±0.3
Type:	Reflective Diffraction Grating
Reflected Wavefront, RMS:	$\lambda/4$
Efficiency (S & P Avg):	70% - 90% @ Blaze Wavelength
Centering of Ruled Area on Substrate:	±1mm
Alignment of Grooves to Edge:	±0.15°
Blaze Wavelength Tolerance (mm):	±25
Groove Spacing Tolerance:	<0.05%

300 Grooves, 1200nm High Performance Reflection Grating
Relative Efficiency to Aluminum



© COPYRIGHT 2018 EDMUND OPTICS, INC. ALL RIGHTS RESERVED