## NOTES:

1. SUBSTRATE: SAPPHIRE (AL2O3) DO NOT MANUFACTURE PARTS TO THIS DRAWING


- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(AVG) ≤0.25% @ 880nm R(AVG) ≤1.25% @ 400 - 870nm R(AVG) ≤1.25% @ 890 - 1000nm



FINE GRIND SURFACE

5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
CLEAR APERTURE	Ø22.86	Ø22.86	
SURFACE FLATNESS	2λ	2λ	
SURFACE QUALITY	80-50 80-50		
BIREFRINGENCE (n <sub>o</sub> -n <sub>e</sub> )	0.008	0.008	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

		B	Edmund Optics®		
THIRD ANGLE PROJECTION	$\phi \lhd$	TITLE	25.4mm Dia., 0.5mm Thick, VIS-NIR AR C Sapphire Window	4mm Dia., 0.5mm Thick, VIS-NIR AR Coated Sapphire Window	
ALL DIMS IN	mm	DWG NO	20834	SHEET 1 OF 1	