





FOCAL LENGTH (EFL): $-18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $-18,49$

- 1 VIS-EXT
 $R(AVG) \leq 0,5\%$ FROM 350 - 700nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 18,857 CV			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R 18,857 CV		
Øe 8,1				Øe 8,1		
SEE NOTE 1				SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 1,93'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE:	NONE λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 9mm Dia x -18mm FL, VIS-EXT Coated, Double-Concave Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26670
					SHEET T SIZE	A4
					SHEET 1 OF 1	