







FOCAL LENGTH (EFL): $40 \pm 0,4$
 BACK FOCAL LENGTH (BFL): $35,63$


SURFACE A			SURFACE B		SURFACE C				
Øe 14			Øe 14		Øe 14				
			CEMENT: NOA 61 OR EQUIVALENT						
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	15mm Dia, x 40mm FL, VIS 0 Coated, Achromatic Lens				
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO		47701	SHEET SIZE A4	SHEET 1 OF 3



1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 26,97±0,027 CX Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BaF10 670/472	R 17,64±0,018 CX Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 15mm Dia, x 40mm FL, VIS 0 Coated, Achromatic Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN:	mm			DWG NO 47701	SHEET SIZE A4
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110								



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 17,64±0,018 CV Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF10 728/284	R 205,03±0,205 CX Øe 14 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 15mm Dia, x 40mm FL, VIS 0 Coated, Achromatic Lens					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm				DWG NO 47701		SHEET SIZE A4	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING										
INDICATIONS IN ACCORDANCE WITH ISO 10110										