


NOTES:

1. TYPE OF MOVEMENT: Linear (X)  
TRAVEL (mm): 26
2. TYPE OF DRIVE: Stepping Motor  
TYPE OF MOTOR: 2-Phase Stepper
3. LOAD CAPACITY (kg): 1
4. RESOLUTION ( $\mu\text{m}$ ): 0.5
5. PITCH ( $\mu\text{rad}$ ):  $\pm 180$   
YAW ( $\mu\text{rad}$ ):  $\pm 150$   
ACCURACY ( $\mu\text{m}$ ): 3  
FLATNESS ( $\mu\text{m}$ ):  $\pm 3$
6. SPEED (mm/s): Maximum: 5
7. REPEATABILITY ( $\mu\text{m}$ ): Bi-directional:  $\pm 1$  Uni-directional: 1



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO  
CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR  
REFERENCE ONLY

**Edmund Optics®**

THIRD ANGLE PROJECTION		TITLE	26mm Travel Precision Compact Motorized Stage	
ALL DIMS IN	mm	DWG NO	88554	SHEET 1 OF 1