NOTES:

- 1. SUBSTRATE: N-BK8
- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: ±3 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE):
 - \$1, \$2, \$3, & \$4: R(AB\$) <0.25% @ 980nm \$5: MULTILAYER DIELECTRIC


4. FINE GROUND SURFACE


5. E

ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61



MARK IDENTIFIES BEAMSPLITTED COATED RIGHT ANGLE PRISM





FOR INFORMATION ONLY:

PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE ACCURACY	λ/4	λ/4	
SURFACE QUALITY	40-21	40-21	
CLEAR APERTURE	> 90%	> 90%	

				Edmund Option	\$S®
THIRD ANGLE PROJECTION TITLE		TITLE	50mm 980nm, Laser Line Polarizing Cube Beamsplitter		
	ALL DIMS IN	mm	DWG NO	48886	SHEET 1 OF 1