


SCHOTT® Fiber Optic Faceplates

New glass compositions for high resolution image transfer!
Offering a greater selection of glasses to meet your specific needs.



Performance Characteristics

Faceplates are used for high resolution, “zero thickness” image transfer applications that include CCD and CMOS coupling, LCD and OLED displays, image intensification, remote viewing, field flattening and x-ray imaging. In opto-electronic applications, faceplates are used as both input and output image intensifier windows.

All SCHOTT faceplates are fabricated to customer-specific requirements. Typical shapes are round or rectangular, and in a variety of sizes up to 320 x 320 mm. Typical element sizes range from as small as 2.5 μm to 25 μm or larger. Faceplates can be manufactured to be vacuum tight.

NEW Glass Compositions for Faceplates


Glass Types*				
Typical Performance Parameters	47A	47A HT	47ARH Radiation hardened	RFG 88
Fiber size (μm)/Resolution lp/mm**	6/102 4/128	6/83	6/102 12/32	6/102 4/128
Numerical Aperture	1.0	1.0	1.0	0.88
Stray Light Control (EMA)	Yes	Yes	Yes	Yes
Collimated Transmission @ 550nm (3mm thick)	73	85	69	73
Coefficient of Thermal Expansion ($\times 10^{-7}/^{\circ}\text{C}$)	68	70	68	63
Density (g/cm^3)	4.15	4.5	4.15	3.41
Core/Clad Ratio	75/25	90/10	75/25 90/10	70/30
Lead Free	Yes	Yes	Yes	Yes
Phosphor Compatible	Yes	Yes	Yes	Yes
Maximum Square Formats (mm)	320	320	320	320

* Other special glass types available upon customer's request



Typical Faceplate Specifications

Typical Performance Parameters	Glass Type						
	24A	24AS	24C	75A	75C	55A	55C
Fiber size (µm)/Resolution lp/mm**	25/23 10/64 8/72 6/102	8/72 6/102 4/128 2.5/203	10/64 6/102 4/128	27/23	6/102	60/10	60/10
Numerical Aperture	1.0	1.0	1.0	0.58	0.58	0.28	0.28
Stray Light Control (EMA)	Yes	Yes	No	Yes	No	Yes	No
Collimated Transmission @ 550nm (3 mm)	70	75	86	60	95	59	95
Coefficient of Thermal Expansion (x10 ⁻⁷ /°C)	68	68	68	61	61	78	80
Density (g/cm ³)	4.0	4.0	4.0	3.05	3.05	2.4	2.4
Core/Clad Ratio	70/30	70/30	70/30	60/40	75/25	60/40	75/25
Lead Free	No	No	No	Yes	Yes	Yes	Yes
Phosphor Compatible	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Maximum Square Formats (mm)	320	320	320	320	320	320	320



** Resolution Measurement performed with a 1951 USAF Resolution Target using diffuse white light illumination. Resolution may vary with other wavelengths.

All specifications are subject to change without prior notice.
This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT.
© SCHOTT AG

Lighting and Imaging
SCHOTT AG
Hattenbergstrasse 10
55122 Mainz
Germany
Phone: +49 (0) 6131/66 7833
Fax: +49 (0) 6131/66 7850
lightingimaging@schott.com
www.schott.com/lightingimaging

