## NOTES:

1. SUBSTRATE: SAPPHIRE (AL2O3) DO NOT MANUFACTURE PARTS TO THIS DRAWING


- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(AVG) ≤1.75% @ 400 - 700nm



FINE GRIND SURFACE

5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

|   | \$1                  | \$2                  |  |
|---|----------------------|----------------------|--|
| SHAPE   | PLANO                | PLANO                |  |
| CLEAR APERTURE                                  | Ø13.50               | Ø13.50               |  |
| SURFACE FLATNESS                                | 2λ                   | 2λ                   |  |
| SURFACE QUALITY                                 | 80-50                | 80-50                |  |
| BIREFRINGENCE (n <sub>o</sub> -n <sub>e</sub> ) | 0.008                | 0.008                |  |
| BEVEL   | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |  |

|                        |             |       | Edmund Optics®  |       |                 |
|------------------------|-------------|-------|---|-------|-----------------|
| THIRD ANGLE PROJECTION |             | TITLE | 15mm Dia., 0.5mm Thick, MgF2 AR Coated<br>Sapphire Window |       |                 |
|                        | ALL DIMS IN | mm    | DWG NO  | 20642 | SHEET<br>1 OF 1 |