



- NOTES:
- 1. SUBSTRATE: N-BK7
  - 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
  - 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: VIS 0° (425-675nm)  
S2: VIS 0° (425-675nm)  
Ravg ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE

- 5. ROHS COMPLIANT
- 6. TRANSMITTED WAVEFRONT (P-V):  
λ/4 (per inch over clear aperture)



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	67.50 x 67.50	67.50 x 67.50
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN mm

**Edmund Optics®**

TITLE

75mm Sq., 2mm Thick, VIS 0° Coated λ/4 N-BK7 Window

DWG NO

23398

SHEET  
16 OF 48