





FOCAL LENGTH (EFL): 60 ±0,6
BACK FOCAL LENGTH (BFL): 56,92

- 1 785nm V-COAT
R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 27,508 CX			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL		
Øe 24				Øe 24		
⌂ SEE NOTE 1				⌂ SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 2,18'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				25mm Dia x 60mm FL, 785NM V- COAT Coated, Plano-Convex Lens		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	25915
			SHEET T SIZE A4			SHEET 1 OF 1