





f' : -100 ± 1

BACK FOCAL LENGTH (BFL): $-101,37$



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 45,846 CV			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL		
Øe 11				Øe 11		
λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00%				λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00%		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ 2,18'				4/ -		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
						
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm	TITLE 12mm Dia x -100mm FL, UV-VIS Coated, Plano-Concave Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO	71101	SHEET SIZE A4	SHEET 1 OF 1