

NOTES:

1. SUBSTRATE:
OPTICAL GRADE GLASS



2. BANDWIDTH: 21nm

3. BLOCKING WAVELENGTH RANGE: 330 - 900nm

4. MINIMUM TRANSMISSION (%): >93 @ 844.5 – 865.5nm

5. ROHS COMPLIANT

NOTE: ARROW ON RING INDICATES PREFERRED DIRECTION OF PROPAGATION OF LIGHT.



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
CONE HALF ANGLE (°)	7	7
OPTICAL DENSITY OD (AVERAGE)	>5	>5
SURFACE QUALITY	80 - 50	80 - 50
CLEAR APERTURE	$\geq \phi 10.00$	$\geq \phi 10.10$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



Edmund Optics®

855nm CWL, >OD5, 30nm FWHM Bandpass
Filter, 25mm Dia.

ALL DIMS IN	mm	TITLE	DWG NO	78458	SHEET 49 OF 52
-------------	----	-------	--------	-------	-------------------