






**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER



| | VALUE |
|--------------------------|-----------------------------------------|
| CENTER WAVELENGTH (nm) | 680nm |
| FULL WIDTH HALF MAX (nm) | 10nm |
| MINIMUM TRANSMISSION | >85 |
| BLOCKING | 200 - 1200 |
| SURFACE QUALITY | 80-50 |
| CONSTRUCTION | MOUNTED IN BLACK ANODIZED ALUMINUM RING |
| COATING TYPE | HARD COATED |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

| | | | | |
|------------------------|----|--------|-----------------------------------------|--------------|
| THIRD ANGLE PROJECTION | | TITLE | OD4, Ø25mm, 680nm x 10nm, HC, BP FILTER | |
| ALL DIMS IN | mm | DWG NO | 88571 | SHEET 1 OF 1 |