





+ 0.4861
x 0.5876
■ 0.6563



SURFACE: INA

DPA: 0.000 MM

SPOT DIAGRAM

CHROMATIC FOCAL SHIFT


45173
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 1.010
GD RADIUS : 1.730
SCALE BAR : 4

REFERENCE : CHIEF RAY


EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45173
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 198.0807 μm
DIFFRACTION LIMITED RANGE: 96.277 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT



POLYCHROMATIC DIFFRACTION MTF

45173
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45173
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM