





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2
SHAPE	PLANO	PLANO
SPECTRAL TRANSMITTANCE $t_{IP}(\%)$	97	97
PASSBAND LIMIT 1 $\lambda_{p1}$ (nm)	950	950
CUT-OFF POSITION $\lambda_c$ (nm)	830±9	830±9
STOPBAND LIMIT $\lambda_s$ (nm)	670	670
WAVELENGTH	IR	IR
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø25.4mm, SCHOTT RG-830 LONGPASS FILTER

DWG NO

32758

SHEET  
1 OF 1