




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | VALUE |
|-------------------------------------|----------------------|
| SHAPE | PLANO |
| SPECTRAL TRANSMITTANCE $\tau_p(\%)$ | 92 |
| PASSBAND LIMIT λ_p (nm) | 520 |
| CUT-OFF POSITION λ_c (nm) | 435±6 |
| STOPBAND LIMIT λ_s (nm) | 370 |
| WAVELENGTH | VIS |
| BEVEL | PROTECTIVE AS NEEDED |

 **Edmund Optics®**

| | | | | |
|--|----|--------|--|--------------|
| THIRD ANGLE PROJECTION  | | TITLE | 50.8 x 50.8mm, SCHOTT GG-435 LONGPASS FILTER | |
| ALL DIMS IN | mm | DWG NO | 32762 | SHEET 1 OF 1 |