


NOTES:




- 1. SUBSTRATE:
FLOAT GLASS
- 2. COATING (APPLY ACROSS COATING APERTURE):
S1: INCONEL
S2: NONE

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



3. FINE GRIND SURFACE

- 4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE
- 5. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|---------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 80-50 | 80-50 |
| BLOCKING WAVELENGTH | 400 - 700 | 400 - 700 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

| | | | |
|------------------------|----|--------|------------------------------------|
| | | | |
| THIRD ANGLE PROJECTION | | TITLE | OD 0.7, Ø25mm REFLECTIVE ND FILTER |
| ALL DIMS IN | mm | DWG NO | 64136 |
| | | | SHEET 1 OF 1 |