





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $t_p(\%)$	93
PASSBAND LIMIT $1 \lambda_{p1} \text{ (nm)}$	620
CUT-OFF POSITION $\lambda_c \text{ (nm)}$	600±6
STOPBAND LIMIT $\lambda_s \text{ (nm)}$	558
WAVELENGTH	VIS
BEVEL	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

TITLE

Ø12.5mm, HOYA R-60 LONGPASS FILTER

DWG NO

66043

SHEET
1 OF 1