




FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	524 & 628 ± 2nm
MINIMUM TRANSMISSION	>90%
BLOCKING	250 - 1100nm
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497A

Edmund Optics®



ALL DIMS IN

mm

TITLE

Ø25mm, 524 & 628nm, DUAL-BAND FILTER

DWG NO

87242

SHEET
1 OF 1