



NOTES:

- 1. SUBSTRATE:  
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)  
S1: Aluminum w/ Protective Overcoat  
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE

3. FINE GRIND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	6.36 x 4.50	4.50 x 4.50
COATING APERTURE	6.36 x 4.50	4.50 x 4.50
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN      mm

Edmund Optics®

TITLE

5mm, Aluminum Coated, N-BK7 High  
Tolerance RA Prism

DWG NO

32540

SHEET  
1 OF 1