





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



	VALUE
OPTICAL DENSITY	≥4.0
CENTER WAVELENGTH (CWL)	1400 ±2.5 nm
FULL WIDTH HALF MAX (FWHM)	12 ±2.5 nm
MINIMUM TRANSMISSION	>70 %
BLOCKING	200 - 1800nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED RING
COATING TYPE	TRADITIONAL COATED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**



ALL DIMS IN	mm	TITLE	Ø25mm, 1400nm x 10nm, MOUNTED BANDPASS FILTER	SHEET 1 OF 1
		DWG NO	65790	