



NOTES:

- 1. SUBSTRATE:  
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)  
S1: ALUMINUM WITH PROTECTED OVERCOAT  
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE

3. FINE GRIND SURFACE

- 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**


SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	95.49 x 67.5	67.5 x 67.5
COATING APERTURE	95.49 x 67.5	67.5 x 67.5
SURFACE FLATNESS	λ/4	λ/4
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

75mm, Aluminum Coated, N-BK7 Right Angle Prism

DWG NO

47233

SHEET  
1 OF 1