

NOTES:



- 1. SUBSTRATE MATERIAL:
N-BK7
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS 0°



R(avg) ≤0.4% @ 425 - 675nm

- 3. FINE GROUND SURFACE
- 4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
- 5. RoHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	 Edmund Optics®				
SHAPE	CONVEX	PLANO					
RADIUS	77.52	∞	EFL	-150	BFL	-151.65	
SURFACE QUALITY	60-40	60-40				TITLE	12.5mm H X 25mm L X -150mm FL VIS 0° COATED, CYLINDER LENS
CLEAR APERTURE	11.50 X 24.00	11.50 X 24.00					
COATING APERTURE	11.50 X 24.00	11.50 X 24.00				TITLE	12.5mm H X 25mm L X -150mm FL VIS 0° COATED, CYLINDER LENS
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					
			ALL DIMS IN	mm	DWG NO	69802	SHEET 1 OF 1