




NOTES:

- 1. SUBSTRATE MATERIAL:
FLOAT GLASS
- 2. COATING (APFLOW ACROSS CLEAR APERTURE):
S1: ALUMINUM
S2: NONE
- 3. BLAZE ANGLE: 6.5°
NOMINAL BLAZE WAVELENGTH: 760nm
GROOVE DENSITY: 300 GROOVES/mm

4. EDGES GROUND

- 5. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

Richardson Gratings™ 300 Grooves, 12.5 x
12.5mm, 760nm, Plane Ruled Reflection
Grating

	S1	S2
SHAPE	PLANO	PLANO
CLEAR APERTURE	11.25 x 11.25	11.25 x 11.25

THIRD ANGLE PROJECTION 	
ALL DIMS IN	mm

TITLE	Richardson Gratings™ 300 Grooves, 12.5 x 12.5mm, 760nm, Plane Ruled Reflection Grating		
DWG NO	37118	SHEET 1 OF 1	