




NOTES:

- 1. SUBSTRATE MATERIAL:
FLOAT GLASS
- 2. COATING (APPLY ACROSS CLEAR APERTURE):
S1: BARE ALUMINUM
S2: NONE
- 3. WAVELENGTH RANGE: 400-700nm
ABSOLUTE DIFFRACTION EFFICIENCY: 45-65%
GROOVE DENSITY: 1800 grooves/mm

- 4. EDGES GROUND
- 5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



			THIRD ANGLE PROJECTION		TITLE		GRATING HOLO 1800GR VIS 25 X 25	
SHAPE	S1 PLANO	S2 PLANO						
CLEAR APERTURE	22.5 x 22.5	N/A	ALL DIMS IN	mm	DWG NO	43222	SHEET 1 OF 1	