




- NOTES:
- 1. SUBSTRATE MATERIAL:
FUSED SILICA
 - 2. SURFACE S1 TO BE PARALLEL TO SURFACE S2 TO WITHIN <3 ARCMIN
 - 3. COATING (APPLY ACROSS COATING APERTURE)


S1: Square Aluminum (AlMgF2) Apertures
R: 70±5% @ 250 - 2000nm @ 45° AOI
T: 30±5% @ 250 - 2000nm @ 45° AOI

S2: NONE
 - 4. POLKA DOT CENTER TO CENTER SPACING : 0.15mm
POLKA DOT MINIMUM APERTURE: 2mm
 - 5. ROHS : COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO		TITLE	BS POLKA-DOT 70/30 25.4mm SQ	
SURFACE QUALITY	80-50	80-50				
CLEAR APERTURE	90%	90%				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	47609
						SHEET 1 OF 1