





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



WAVELENGTH RANGE(nm)	400 - 700
DIFFUSING ANGLE (°)	6
CLEAR APERTURE CA (mm)	5
FREQUENCY (Hz)	300
POWER SUPPLY	Micro-USB
OPERATING VOLTAGE (V)	5
OPERATING TEMPERATURE (°C)	-20 to 65
STORAGE TEMPERATURE (°C)	-40 to 100

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]



ALL DIMS IN

mm

TITLE

6° Diffusion Angle, 5mm CA Laser Speckle
Reducer, VIS

DWG NO

88390

SHEET
1 OF 1