





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING




BANDPASS FILTER



REV. A	VALUE
CENTER WAVELENGTH (CWL)	633nm ± 1 nm
FULL WIDTH HALF MAX (FWHM)	5.0 ± 1 nm
MINIMUM TRANSMISSION	$\geq 85\%$
BLOCKING	200 - 1200nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497a, SEC 3.4.1
ENVIRONMENTAL	MIL-STD-810F, SEC 507.4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	633nm CWL, 50mm Dia., Hard Coated OD4 5nm Bandpass Filter	
ALL DIMS IN	mm	DWG NO	39379	SHEET 1 OF 1